

Mått

H: 311 mm

B: 50 mm

D: 23 mm

Vikt: 340g

Mikrobrytare:

- Liten tryckyta (61mm): 1st NO / NC

- Stor tryckyta (227mm): 1st NO

IP klass: IP67

Nominell märkström från:

12 V Resisitiv 6A

Induktiv L/R 5 ms 6A

24 V Resisitiv 6A

Induktiv L/R 5 ms 5A

Lägsta märkström 1mA/4 V DC



Material:

Alu.6060-T6

POM Plast (Acetalplast)

Rengöring:

Kontakten går att rengöra med alla förekommande rengöringsmedel.

Tillval:

Går att beställa med:

- * Radiostyrning
- * Universiella symboler:
 - 1. Dörrsymbol



2. Rullstolsymbol



3. Hissymbol




* Kontrastränder



OBS.

Vid utomhusmontage bör ett 3mm dräneringshål borras i den nedre gaveln på armbågskontakten för att dränera ut eventuell fukt.




Installation instructions JCK 260



Assembly and installation.

- Disassemble the lower endcap by screwing out both screws.
- 2. Slide out the aluminum lid.
- 3. Connect the electric wiring (12-24 V) to the connection terminals.
- 4. Fixate the aluminum core with assembly screws and washers.
- 5. Assemble the lower end cap.
- 6. Place back the lid by setting its hinge on the core's C channel and turning it counterclockwise (see illustration).



Click here to go to the product JCK 260.